

SPECIFICATION

LED DOMO Armatur FLAT PRO

Product Details



Application

- Supermarket
- Meeting room
- Warehouse
- Office
- Library
- Museum
- Hotel
- Exhibition hall
- Store

Features

- Slim Design, UGR less 19
- Beam Angle: 2*45° lens
- Black color Aluminium+lens
- 145lm/w \pm 5%, up to 180lm/w
- Available in Non-dimmable&0/1-10V&Dali
- Energy saving up to 80%
- Suspending&Ceiling mounted&Trackway for convenient installation


Temperature

Operating: - 25 ~ + 40°C

Storage: - 40 ~ + 85°C



Dimension



| Dimension | A | B | C |
|-----------|--------|-------|------|
| 600mm | 584mm | 125mm | 13mm |
| 1200mm | 1164mm | 125mm | 13mm |
| 1500mm | 1454mm | 125mm | 13mm |

Technical Data sheet

| | Power | Dimension | Input | LEDS | Beam angle | CCT | Light efficiency | CRI | Lumen output |
|--|-------|-----------|------------|------|------------|-------------------------------|------------------|-----|--------------|
| | 40W | 600mm | AC200-240V | 132 | 2*45° lens | 3000K / 4000K / 5000K / 6000K | 145lm/w±5% | >80 | 5800lm±5% |
| | 60W | 1200mm | AC200-240V | 264 | 2*45° lens | 3000K / 4000K / 5000K / 6000K | 145lm/w±5% | >80 | 8700lm±5% |
| | 75W | 1500mm | AC200-240V | 330 | 2*45° lens | 3000K / 4000K / 5000K / 6000K | 145lm/w±5% | >80 | 10850lm±5% |

Packing information


| Dimension | Carton Size | N.W./Pieces | G.W./Carton | Pieces/Carton | Maximum Loading of | | |
|-----------|----------------|-------------|-------------|---------------|--------------------|----------|----------|
| | | | | | 20'GP | 40'GP | 40'HQ |
| 600mm | 630*350*190mm | 1.8kg | 12kg | 5pcs | 650CTNs | 1350CTNs | 1700CTNs |
| 1200mm | 1230*350*190mm | 2.8kg | 17kg | 5pcs | 325CTNs | 675CTNs | 850CTNs |
| 1500mm | 1530*350*190mm | 3.3kg | 20kg | 5pcs | 260CTNs | 540CTNs | 680CTNs |

Installation

Suspending




Ceiling mounted



Trackway



Seamless



Caution:

- ☒ Please read the use manual before the installation
- ☒ Please do not stare directly at the lamp surface
- ☒ Please do not cover anything on the lamp and keep it away from the high temperature area.
- ☒ The lamp is only suitable for the weak acid and weak base environment